

corpro

a better fit

Core Product Data










HM1400 Half Mask










EN Requirement		Small	Medium	Large	
Weight	Actual	111 g	116 g	117 g	
Temperature Conditioning	EN	24 hrs in a dry atmosphere at 70 °C followed by 24 hrs at -30 °C			
Flammability	EN	The Half Mask is passed through a single burner, set up with a 40 mm, 800 °C flame, at a constant speed of 60mm/s at a distance of 20 mm between the burner and lowest part of the facepiece. The facepiece cannot continue to burn 5 s after removal.			
Head Harness Pull Test	EN	Withstand a pull of 50 N for 10 s			
Connectors Pull Test	EN	Withstand a pull of 50 N for 10 s			
Breathing Resistance		Inhalation Resistance		Exhalation Resistance	
		30 l/min	95 l/min	160 l/min	
	Actual	0.11 mbar	0.42 mbar	0.77 mbar	
	EN	< 0.50 mbar	< 1.3 mbar	< 2.00 mbar	
CO ₂ Content of Inhaled Air	Actual	0.66 %		0.64 %	
	EN	< 1.00 %			
Inward Leakage - Based on average of the 10 subjects per exercise.		Exercise			
		Walk	Head side/side	Head up/down	Talk
	Actual	0.060 % ¹	0.115 % ²	0.073 % ³	0.247 % ¹
	EN	< 5.000 %			Mean
					0.141 % ³
					< 2.000 %
		Notes			
		¹ 5 Subjects achieved results < 0.001 %			
		² 4 Subjects achieved results < 0.001 %			
		³ 3 Subjects achieved results < 0.001 %			

FFM1600 Full Face Mask

EN Requirement		Small	Medium	Large	
Weight	Actual	580 g	584 g	589 g	
Leak Tightness	EN	A negative pressure of 10 mbar is applied to the mask, the mask must not leak more than 1 mBar in 1 min.			
Temperature Conditioning	EN	72 hrs in a dry atmosphere at 70 °C followed by 72 hrs at 70 °C at 95-100 % relative humidity followed by 24 hrs at -30 °C			
Flammability	EN CL1	The Full Face Mask is passed through a single burner, set up with a 40 mm, 800 °C flame, at a constant speed of 60 mm/s at a distance of 20 mm between the burner and lowest part of the facepiece. The facepiece cannot continue to burn 5 s after removal.			
	EN CL2	The Full Face Mask is placed directly above 6 burners each set at a distance of 250 mm from the mask surface, the flames are set at 950 °C, the mask is held in the flame static for 5 s. Upon removal from the flame the facepiece cannot continue to burn 5 s after removal.			
Head Harness Pull Test	EN CL1	Withstand a pull of 100 N for 10 s			
	EN CL2	Withstand a pull of 150 N for 10 s			
Inhale Connectors Pull Test	EN CL1	Withstand a pull of 250 N			
	EN CL2	Withstand a pull of 500 N			
Exhale Connectors Pull Test	EN CL1	Withstand a pull of 50 N for 10 s tested 10 consecutive times			
	EN CL2	Withstand a pull of 150 N for 10 s tested 10 consecutive times			
Field of Vision	Actual	Effective 91.3 % , Overlapped 92.4 %			
	EN	Effective > 70 % , Overlapped > 80 %			
Breathing Resistance		Inhalation Resistance		Exhalation Resistance	
		30 l/min	95 l/min	160 l/min	
	Actual	0.12 mbar	0.43 mbar	0.77 mbar	
	EN	< 0.50 mbar	< 1.3 mbar	< 2.00 mbar	
		Following 300 l/min exhalation flow			
		Inhalation Resistance		Exhalation Resistance	
		30 l/min	95 l/min	160 l/min	
	Actual	0.11 mbar	0.40 mbar	0.80 mbar	
	EN	< 0.50 mbar	< 1.3 mbar	< 2.00 mbar	
		Following 80 mbar negative pressure			
		Inhalation Resistance		Exhalation Resistance	
		30 l/min	95 l/min	160 l/min	
Actual	0.10 mbar	0.33 mbar	0.54 mbar		
EN	< 0.50 mbar	< 1.3 mbar	< 2.00 mbar		
CO ₂ Content of Inhaled Air	Actual	0.70 %		0.75 %	
	EN	< 1.00 %			
Inward Leakage - Based on average of the 10 subjects per exercise.		Exercise			
		Walk	Head side/side	Head up/down	Talk
	Actual	0.006 % ¹	0.006 % ²	0.006 % ³	0.007 % ²
	EN	< 0.050 %			Mean
					0.004 % ²
					< 2.000 %
		Notes			
		¹ 4 Subjects achieved results < 0.001 %			
		² 5 Subjects achieved results < 0.001 %			
		³ 6 Subjects achieved results < 0.001 %			

F1100 Filter Range

The F1100 Filter Range - For use with both the FFM1600 and HM1400 masks											
		Particulate Only Filter	Gas Only Filter					Combined Filter			
											
EN Requirement		P3 R	A1	A2	ABE1	ABEK1	A1P3 R D	A2P3 R D	ABE1P3 R D	ABEK1P3 R D	
Weight per filter pair	Actual	125 g	210 g	210 g	230 g	230 g	250 g	250 g	280 g	280 g	
	EN140	< 300 g									
	EN136	< 500 g									
Pressure Drop (Measurement at 95 litres per minute)	Actual	0.9 mbar	0.9 mbar	1.2 mbar	1.0 mbar	1.0 mbar	1.7 mbar	1.9 mbar	1.8 mbar	1.8 mbar	
	EN	4.2 mbar	4.0 mbar	5.6 mbar	4.0 mbar	4.0 mbar	8.2 mbar	9.8 mbar	8.2 mbar	8.2 mbar	
Efficiency	Actual	> 99.99 %	NA					> 99.99 %			
	EN	> 99.95 %	NA					> 99.95 %			
Penetration	Actual	< 0.01 %	NA					< 0.01 %			
	EN	< 0.05 %	NA					< 0.05 %			
Cyclohexane	Actual	NA	200 min	50 min	150 min	150 min	200 min	50 min	150 min	150 min	
	EN		70 min	35 min	70 min	70 min	70 min	35 min	70 min	70 min	
Hydrogen Cyanide	Actual		NA		> 100 min	> 100 min	NA	NA	> 100 min	> 100 min	
	EN		NA		25 min	25 min			25 min	25 min	
Hydrogen Sulphide	Actual		NA		> 100 min	> 100 min	NA	NA	> 100 min	> 100 min	
	EN		NA		40 min	40 min			40 min	40 min	
Chlorine	Actual		NA		> 100 min	> 100 min	NA	NA	> 100 min	> 100 min	
	EN		NA		20 min	20 min			20 min	20 min	
Sulphur Dioxide	Actual		NA		65 min	50 min	NA	NA	65 min	50 min	
	EN		NA		20 min	20 min			20 min	20 min	
Ammonia	Actual	NA				90 min	NA			90 min	
	EN	NA				50 min	NA			50 min	
Viral Filtration Efficiency (VFE)	Actual	> 99.9999 %	NA				> 99.9999 %				

Filter usage at a glance										
										
		P3 R	A1	A2	ABE1	ABEK1	A1P3 R D	A2P3 R D	ABE1P3 R D	ABEK1P3 R D
Organic vapours	A	NA	✓	✓	✓	✓	✓	✓	✓	✓
Inorganic vapours	B		NA		✓	✓		NA	✓	✓
Acidic vapours	E		NA		✓	✓		NA	✓	✓
Ammonia vapours	K		NA		✓	✓		NA	✓	✓
Nuisance odours		NA	✓	✓	✓	✓	✓	✓	✓	✓
Dusts	P	✓			NA		✓	✓	✓	✓
Mists		✓			NA		✓	✓	✓	✓
Viruses such as COVID-19		✓			NA		✓	✓	✓	✓
Water based painting		✓			NA		✓	✓	✓	✓
Solvent based brush painting		NA	✓	✓	✓	✓	✓	✓	✓	✓
Rubbing down paint		✓			NA		✓	✓	✓	✓
Paint stripping, chemical or heat					NA		✓	✓	✓	✓
White spirit		NA	✓	✓	✓	✓	✓	✓	✓	✓
Chlorine (cleaning & pools)			NA		✓	✓		NA	✓	✓
Glyphosate (weed killer)		✓			NA		✓	✓	✓	✓
Brick acid (graffiti removal)			NA		✓	✓		NA	✓	✓
Formaldehyde			NA		✓	✓		NA	✓	✓
Fibres & fibre glass		✓			NA		✓	✓	✓	✓
Plaster		✓			NA		✓	✓	✓	✓
Silica (concrete/stone cutting)		✓			NA		✓	✓	✓	✓
Woods (hard & soft)		✓			NA		✓	✓	✓	✓
MDF (machine tooling)		✓			NA		✓	✓	✓	✓
Welding (ferrous & lead)		✓			NA		✓	✓	✓	✓
Earth moving (contaminated)					NA	NA			✓	✓


WEL or Workplace Exposure Level - This table is for guidance purposes only. A proper risk assessment by qualified personnel should be carried out before selecting an appropriate filter cartridge.

Up-and-coming product data will be released in due course. Please see product leaflets for more information.

 www.corpro.systems  sales@corpro.systems  +44 (0) 1942 597 267

 1A Millfield Lane, Haydock, St Helens, WA11 9TW, United Kingdom

GENTEX
CORPORATION

 @Corpro_Systems

   Search 'Corpro'

